

The EPD® Mk2 combines unequalled radiological performance with advanced software and hardware features.

EPD® Mk2 Electronic Personal Dosimeter

- Advanced radiological performance
- Detector technology based upon the well proven EPD® Mk1
- Small and lightweight
- Ergonomic rugged design



The EPD® Mk2 is suitable for use as a single stand-alone dosimeter or as part of a comprehensive dosimetry management system using renowned hardware and software packages. The high quality and standard battery contribute to competitive lifetime costs.

- Multi-detector technology
- Excellent response to gamma, beta and X-radiation
- Loud, configurable audible alarm.
- Rapid Infra-red communications to reader/PC or stand-alone operation
- Excellent immunity to electromagnetic interference
- Easy to read display with optional backlighting
- Advanced radiological performance, 15 keV to 10 MeV

System Specifications

Radiological

- Sensitive to X and μ radiation, β particles
- Direct readout of dose equivalents $H_p(10)$ (deep/whole body) and $H_p(0.07)$ (shallow/skin)
- Display Units: Sv and rem (with prefixes), OR scaled in Sv and cGy (with prefixes)
- Neutron response <2%
- Dose display and storage 0 μ Sv to >16 Sv (0 mrem to >1600 rem) auto ranging
- Resolution for display 1 μ Sv (0.1 mrem), up to 10 mSv (1 rem)
- Resolution for storage 1/64 μ Sv (=1.5 μ rem)
- Dose rate display 0 μ Sv/h to >4 Sv/h (0 mrem/h to >400 rem/h) auto ranging
- Alarms dual $H_p(10)$ dose and dose rate alarms; $H_p(0.07)$ dose and dose rate alarms
- Energy response:

Photon, $H_p(10)$
 $\pm 50\%$ 15 keV to 17 keV (ref. ^{137}Cs)
 $\pm 20\%$ 17 keV to 15 MeV (ref. ^{137}Cs)
 $\pm 30\%$ 15 MeV to 6 MeV (ref. ^{137}Cs)
 $\pm 50\%$ 6 MeV to 10 MeV (ref. ^{137}Cs)

Photon, $H_p(0.07)$
 $\pm 30\%$ 20 keV to 6 MeV (ref. ^{137}Cs)
 $\pm 50\%$ 6 MeV to 10 MeV (ref. ^{137}Cs)

Beta, $H_p(0.07)$
 $\pm 30\%$ 250 keV to 1.5 MeV E (ref. $^{90}\text{Sr}/^{90}\text{Y}$)

- Angular response:

$H_p(10)$ ^{137}Cs $\pm 20\%$ up to $\pm 75^\circ$
 $H_p(10)$ ^{241}Am $\pm 50\%$ up to $\pm 75^\circ$
 $H_p(0.07)$ $^{90}\text{Sr}/^{90}\text{Y}$ $\pm 30\%$ up to $\pm 55^\circ$

- Accuracy

$H_p(10)$ ^{137}Cs
 $\pm 10\%$ $H_p(0.07)$ $^{90}\text{Sr}/^{90}\text{Y}$ $\pm 20\%$

- Dose rate linearity:

$H_p(10)$ ^{137}Cs
 $\pm 10\%$ <0.5 Sv/h (<50 rem/h)
 $\pm 20\%$ 0.5 Sv/h to 1 Sv/h (50 to 100 rem/h)
 $\pm 30\%$ 1 Sv/h to 2 Sv/h (100 to 200 rem/h)
 $\pm 50\%$ 2 Sv/h to 4 Sv/h (200 to 400 rem/h)
Between 4 Sv/h and 50 Sv/h
continues to accumulate dose at a rate > 4Sv/h

$H_p(0.07)$ $^{90}\text{Sr}/^{90}\text{Y}$
 $\pm 20\%$ <1Sv/h (<100 rem/h)
Between 1Sv/h and 50 Sv/h
continues to accumulate dose at a rate > 1Sv/h

Memory

- 10 year data retention without battery
- Short term dose registers for $H_p(10)$ and $H_p(0.07)$
- Approved Dosimetry Service (Dose of Record) dose memory area with password protection
- Peak dose rates with time of occurrence
- All stored times have 1 second resolution
- Count down timer, 1 hour 39 minutes 59 seconds maximum, resolution 1 second
- Event log, 23 entries for time recording of alarms, etc., for incident assessments
- Dose profile history: settable interval from 2 seconds to 35 hours, stores transitions of $H_p(10)$ and $H_p(0.07)$ at a resolution of 1 μ Sv (0.1 mrem); will store up to 579 records for transitions up to 127 μ Sv or less

Alarms

- Audible and visual alarms for dose, dose rate, count down time, read time and failure modes.
- $H_p(10)$ dose chirp settable from 0.01 μ Sv/chirp to 100 μ Sv/chirp (1 μ rem to 10 mrem/chirp)

Electrical and Mechanical

- Power supply: single AA battery 1.5 V alkaline cell for up to 30 weeks continuous operation, OR 3.6 V lithium for typically 5-10 months continuous operation (interchangeable) (depending on battery type)
- Alarm sounder: fully sealed typically 98 dB(A) at 20 cm with multiple modes
- Communications: IR interface up to 1 meter range (39")
- Display and function control by a single button on front (recessed to prevent inadvertent operation)
- Size: 85 x 63 x 19 mm (3.3" x 2.5" x 0.8") excluding clip
- Weight: 95 g (3.2 oz) including battery and clip
- Case material: high impact polycarbonate/ABS blend

Environmental

- Operating temperature:
-10 °C to +40 °C
(+15 °F to +105 °F)
- Humidity: 20% to 90% RH non-condensing
- Vibration: IEC 1283: 2g, 15min., 10 to 33 Hz
- Shock: 1.5 m (5') drop on each surface onto concrete
- EMI/EMC: Exceeds MIL STD 461D RS103

©2007 Thermo Fisher Scientific Inc. All rights reserved. Kapton is a registered trademark of of E.I. du Pont de Nemours and Company. All other trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Results may vary under different operating conditions. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representatives for details. Literature Code LITEPD Mk2 0407

Worldwide
Frauenauracher Strasse 96 +49 (0) 9131 909-0
D 91056 Erlangen, Germany +49 (0) 9131 909-205 fax

United Kingdom
Bath Road, Beenham, +44 (0) 118 971 2121
Reading RG7 5PR United Kingdom +44 (0) 118 971 2835 fax

United States +1 (508) 520-2815
27 Forge Parkway +1 (800) 274-4212 toll-free
Franklin, MA 02038 USA +1 (508) 428-3535 fax

www.thermo.com/rmp

Thermo
SCIENTIFIC